

**TESA****Digital dial indicator 0.01 mm reading, Measuring range: 12,5mm****Order data**

Order number	434260 12,5
GTIN	7630041111170
Item class	45A

Description**Version:**

Digital dial indicator with combined scale and digital display (10 mm character height) and mechanical tolerance marks.

Function:

Automatic switch-off, measurement value output, reversible direction of measurement. Button panel can be locked.

Supplied with:

1 battery No. 081560 size CR2032

Optional extras:

Spare and special contact points No. 434900; 434910; 434915. Data cable No. 498950.

Technical description

Gauging force	$\leq 2 \text{ N}$
Thickness of housing	27 mm
Calibration	C1
Measuring range	12.5 mm

Data sheet

Body Ø	57 mm
Clamping shank Ø h6	8 mm
Reversible reading	0.0005 in
Reversible reading	0.01 mm
Error limit	0.02 mm
#Number of batteries contained	1
#Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Standard	DIN 878
Reversible reading	mm / inch
Interface	RS232C interface
Interface	USB interface
Measurement technology	digital
Type of product	dial gauge

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/434260-12,5>