

**Digital absolute dial indicator 0.001 mm reading, Measuring range: 12,5mm****Order data**

Order number	434460 12,5
GTIN	4946368586472
Item class	44A

Description**Version:**

Precision measuring system with glass scale: Speed of movement has no influence on the measured result, measured value is not lost even on switching off. Low power consumption. Graphical display for tolerance comparison. **A factor can be input for the measurement value.**

Callout:

Display rotates 330°

Supplied with:

1 battery No. 081560 size 357.

Optional extras:

Data cable No. 497080, special contact points No. 434900; 434910; 434915.

Technical description

Body Ø	61 mm
Thickness of housing	39 mm
Clamping shank Ø h6	8 mm
Measuring range	12.5 mm

Gauging force	1.2 N
Calibration	C1
Error limit	0.003 mm
Selectable display	0.01 / 0.001 mm
#Article no of the battery / rechargeable battery fitted	081560 357
#Number of batteries contained	1
Power supply	Battery-powered
Standard	Manufacturer's standard
Interface	USB interface
Interface	Digimatic interface
Measured value saving	once-off setting of the zero position
Measurement technology	digital
Type of product	dial gauge

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/434460-12,5>