

ALLURIS

Precision hand-held tachometer, Type: C



Order data

Order number	471300 C
GTIN	4260244680222
Item class	47F

Description

Version:

Precision hand-held tachometer in **sturdy die-cast aluminium casing**. Large digital display, easy to use. Lengths and speeds in selectable international units. High-precision **contact tachometer** (60 impulses / revolution). Especially suitable for measuring low speeds.

Application:

Rotational speed measurement: 0.1 – 99999 rpm (mechanically up to 25,000 rpm).

Speed: 0.1– 3810 m/min

Length measurement: 0.0– 99999 m/min

Counting: 0– 99999

Supplied with:

Includes 2 measuring tips, 6 inch measuring wheel, female centre, extension shaft, operating instructions, protective case, 2 batteries No. 081561 size LR6.

Optional extras:

Reflector strips No. 471315.

Technical description

Impulses per revolution (contact measurement)	60
Measurement time	1 s
Surface disc circumference	6 in
Error limit	0.006 (± 0.5 digit) %

Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081561 LR6
Power supply	Battery-powered
Measurement technology	digital
Calibration	I2
Type of product	Hand-held tachometer

Services

CalibrationTachometer / stroboscope Type D	027900 D
--	----------

Accessories

Alkaline-manganese batteries International size LR6	081561 LR6
Reflector strip set35 pieces	471315