



Multimeter, Device type: 9917



Order data

Order number	473320 9917
GTIN	4045197554291
Item class	42I

Description

Version:

Ergonomically shaped two-component casing with rubber cover. Large easy-to-read digital display with switchable background lighting. Auto ranging meters. All meters with test prod mounting on the rear for one-hand operation, with a stand.

Function:

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

Application:

Digital service meters with comprehensive functions.

Standard:

IEC / DIN EN 61010-1; GS TÜV Rheinland und CE Zeichen.

Supplied with:

Supplied with batteries (2 pcs. size 960, 1 pc. size 9917), test prods No. 473328 size 2.

Temperature sensor, cover caps, and carrying case.

IP Index of Protection: IP 67

Information displayed: 4000

Display backlit: yes

Basic accuracy: 1.5 %

acoustic continuity test: yes

Diode testing: yes
Measurement process: RMS

Technical description

Frequency	0.001 Hz – 9.9 MHz
Information displayed	4000
Overvoltage category	CAT IV 600 V; CAT III 1000 V
AC current	0,1 μ A – 10 A
AC voltage	0.1 mV – 1000 V
Basic accuracy	1.5 %
DC current	0,1 μ A – 10 A
IP Index of Protection	IP 67
Diode testing	yes
Resistance	0.1 Ω – 40 M Ω
DC voltage	0.1 mV – 1000 V
acoustic continuity test	yes
Measurement process	RMS
Manufacturer's designation	9917
Data storage key	yes
Display backlit	yes
Temperature	-20 - 760 $^{\circ}$ C
Capacitance	1 pF – 200 μ F
automatic power-off	yes
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081551 6LR61
Power supply	Battery-powered
Power supply	No. 081556 size 6LR61
Type of product	Multimeter

Services

Labelling laser-etched Type

018940

Accessories

Test leads Measuring tips Ø 2 mm

473328 2

Alkaline-manganese batteries International size 6LR61

081556 6LR61