

**Small dial indicator 0.001 mm reading, Measuring range: 12,5mm****Order data**

Order number	434035 12,5
GTIN	7640125711646
Item class	46A

Description**Version:**

Very small digital dial indicator (casing Ø 44 mm) with patented inductive measuring system. Battery life > 3500 h. Comprehensive functionality: ABS and relative mode, PRESET. With additional dovetail slide fitted on the back.

Supplied with:

1 battery No. 081560 size CR2032.

Optional extras:

Opto RS232 data cable with 9-pin serial connection and combined external power supply No. 498951.

Technical description

Thickness of housing	19 mm
Calibration	C1
Clamping shank Ø h6	8 mm
Gauging force	0.5 – 0.9 N
Body Ø	44 mm

Data sheet

Measuring range	12.5 mm
Error limit	0.005 mm
#Number of batteries contained	1
#Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Standard	Manufacturer's standard
Reversible reading	mm / inch
Interface	RS232 interface
Measurement technology	digital
Type of product	dial gauge

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/434035-12,5>