

Mitutoyo**Digital absolute dial indicator 0.001 mm reading, Measuring range: 25mm**

Order data

Order number	434460 25
GTIN	4946368586700
Item class	44A

Description

Version:

Precision measuring system with glass scale: Speed of movement has no influence on the measured result, measured value is not lost even on switching off. Low power consumption. Graphical display for tolerance comparison. **A factor can be input for the measurement value.**

Callout:

Display rotates 330°

Supplied with:

1 battery No. 081560 size 357.

Optional extras:

Data cable No. 497080, special contact points No. 434900; 434910; 434915.

Measured value saving: once-off setting of the zero position

Calibration: C1

Selectable display: 0.01 / 0.001 mm

Error limit: 0.003 mm

Gauging force: 1.8 N

Clamping shank \varnothing h6: 8 mm

Body \varnothing : 61 mm

Thickness of housing: 39 mm

Technical description

Calibration	C1
Body Ø	61 mm
Measuring range	25 mm
Thickness of housing	39 mm
Gauging force	1.8 N
Clamping shank Ø h6	8 mm
Error limit	0.003 mm
Selectable display	0.01 / 0.001 mm
Article no of the battery / rechargeable battery fitted	081560 357
Number of batteries contained	1
Power supply	Battery-powered
Standard	Manufacturer's standard
Interface	USB interface
Interface	Digimatic interface
Measured value saving	once-off setting of the zero position
Measurement technology	digital
Type of product	dial gauge

Services

Calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 30 mm	013210 30
Labelling laser-etched Type	018940
DAkkS calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 100 mm	013250 100
DAkkS calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 100 mm	023010 100
Calibration Dial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 30 mm	023000 30

Accessories

Carbide contact point Type 18/4	434910 18/4
Extension for measuring probe Length L 70 mm	434920 70
Steel contact point Type 17	434900 17
Steel contact point Type 24	434900 24
Steel contact point Type 18/6	434900 18/6
Angled bracket for dial indicator 60° Clamping length 25 mm	434918 25
Multi-receiver / USB keyboard interface Type	498975
Pivoting contact point	434912
Connecting cable Type USB2	497080 USB2
Extension for measuring probe Length L 20 mm	434920 20
Steel contact point Type 14/30	434900 14/30
Steel contact point Type 18/4	434900 18/4
Steel contact point Type 14	434900 14
Steel contact point Type 11/15	434900 11/15
Extension for measuring probe Length L 40 mm	434920 40
Button cell / special battery Battery type 357	081560 357
Steel contact point Type 13	434900 13
Steel contact point Type 20	434900 20
Angled bracket for dial indicator 60° Clamping length 50 mm	434918 50
Carbide contact point Type 10	434910 10
Steel contact point Type 15	434900 15
Extension for measuring probe Length L 60 mm	434920 60
Steel contact point Type 16	434900 16
Steel contact point Type 11/35	434900 11/35
Steel contact point Type 29/20	434900 29/20
Steel contact point Type 11/30	434900 11/30
Carbide contact point Type 18/5	434910 18/5

Steel contact point Type 14/20	434900 14/20
Extension for measuring probe Length L 50 mm	434920 50
Extension for measuring probe Length L 90 mm	434920 90
Carbide contact point Type 16	434910 16
Steel contact point Type 12	434900 12
Steel contact point Type 30/10	434900 30/10
Steel contact point Type 39	434900 39
Angled bracket for dial indicator 45° Clamping length 25 mm	434917 25
Carbide contact point Type 18/1	434910 18/1
Ruby contact point Type 2	434915 2
Extension for measuring probe Length L 80 mm	434920 80
Steel contact point Type 10	434900 10
Receiver / USB keyboard interface Type	498965
Steel contact point Type 14/40	434900 14/40
Steel contact point Type 2	434900 2
Steel contact point Type 18/2	434900 18/2
Steel contact point Type 18/1	434900 18/1
Connecting cable with data switch Type D1	497100 D1
Steel contact point Type 11/25	434900 11/25
Steel contact point Type 28	434900 28
Steel contact point Type 29/10	434900 29/10
Steel contact point Type 11/20	434900 11/20
Carbide contact point Type 18/6	434910 18/6
Connecting cable Type D2	497080 D2
Transmitter Type S1	498966 S1
Steel contact point Type 11	434900 11
Steel contact point Type 18/5	434900 18/5
Steel contact point Type 14/15	434900 14/15
Carbide contact point Type 18/2	434910 18/2

Carbide contact point Type 2	434910 2
Connecting cable with data switch Type USB2	497100 USB2
Connecting cable with data switch Type D2	497100 D2
Steel contact point Type 18/3	434900 18/3
Connecting cable Type D1	497080 D1
Extension for measuring probe Length L 15 mm	434920 15
Extension for measuring probe Length L 30 mm	434920 30
Carbide contact point Type 18/3	434910 18/3
Carbide contact point Type 11	434910 11
Angled bracket for dial indicator 45° Clamping length 50 mm	434917 50
Extension for measuring probe Length L 10 mm	434920 10
Carbide contact point Type 14	434910 14
Extension for measuring probe Length L 100 mm	434920 100
Carbide contact point Type 17	434910 17