

HOLEX**Set of parallels with clamping clip, Type: 125****Order data**

Order number	366730 125
GTIN	2050001742476
Item class	38F

Description**Version:**

Accuracy: Plan parallelism height tolerance ± 0.01 mm; **hardness:** 57 HRC. Insert the clamping clips into the clamp blocks and click them on to the vice.

Advantage:

The clamp blocks remain in position during machining and after the high pressure vice has been opened.

Suitable for:

All GARANT, Allmatic NC high pressure vices with tenon width (dimension A) $39 \text{ mm} \pm 0.1 \text{ mm}$.

Supplied with:

Supplied with plastic stand, 10 pairs of inserts, 4 clamping clips

Optional extras:

Spare clamping levers No. 366731 in the spare parts list.

Note:

Check dimension A on the high pressure vice!

Technical description

Width	3 mm
Length	125 mm
Height	25 mm

Height	30 mm
Height	33 mm
Height	10 mm
Height	37 mm
Height	15 mm
Height	35 mm
Height	28 mm
Height	36 mm
Height	20 mm
suitable for colour code	Titan
suitable for colour code	Titan 2
suitable for colour code	Duo Plus
suitable for colour code	Duo
suitable for colour code	TC
suitable for colour code	LC
suitable for colour code	LC-GARANT
suitable for colour code	LCV125G
Number of strips	10 pair
Type of product	Pairs of parallels

Accessories

Clamping clip set(4 pieces)	366731
-----------------------------	--------