



## Measuring gauge for internal tapers IFM, Measuring range: 0,5-20mm



### Order data

Order number	435172 0,5-20
GTIN	2050001055743
Item class	46D

### Description

#### Version:

IFM internal taper measuring gauge with 90° anvil cone for **determining the largest internal taper  $\varnothing$** . The hardened anvil cone cross is inserted into the internal taper. The largest  $\varnothing$  is determined by pressing until reaching the stop.

#### Supplied with:

Dial indicator.

#### Note:

Special versions with other taper angles available on request. Measuring devices for measuring the chamfer length available on request. Dial indicator and base body available separately.

### Technical description

Measuring range	0.5 - 20 mm
Scale graduations	0.01 mm
Standard	DIN 878
all parts	hardened

Packaging	sturdy box
Calibration	Price on request
Type of product	Taper measuring gauge

**Services**

CalibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 30 mm	023000 30
---	-----------