



Humidity and temperature measuring tool, Type: 608H1



Order data

Order number	474050 608H1
GTIN	4029547000324
Item class	47B

Description

Version:

For exact determination of **humidity, temperature, and dew point**. Insensitive to condensation, maintenance-free. **Min / max display** with Reset function. Can be used free-standing or hung up.

Application:

Ideal for monitoring room air conditioning.

Supplied with:

Supplied with battery No. 081561 size 6LR61 and calibration certificate.

Technical description

Relative humidity measurement range	10 - 95 %
Temperature measurement range	0 - 50 °C
Error limit relative humidity	3 %
Measuring range dew point td	-20 - 50 °C
Resolution temperature (0 – 50 °C)	0.1 °C
Height	90 mm

Depth	40 mm
Width	111 mm
Error limit dew point td	±0.5 (at 25 °C) °C
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081561 6LR61
Power supply	Battery-powered
Calibration	I6
Type of product	Temperature and humidity measuring device

Services

CalibrationThermo-hygrometer Type A	027660 A
DAkkS calibrationThermo-hygrometer Type A	027670 A