



## Infrared thermometer, Type: T4



### Order data

Order number	474012 T4
GTIN	4029547011702
Item class	47B

### Description

#### Version:

Quick contact-less measurement over distances.

- **Display: Min / max function**
- **Limit value monitoring with optical and acoustic alarm.**
- **Small and handy with illuminated display.**
- **Quick measurement: 2 measurements/s.**

Real measuring spot marking by **2 laser points.**

Precise contact measurement.

#### Supplied with:

Supplied with test certificate and 1× battery No. 081561 size 6LR61.

#### Optional extras:

Protective case No. 474029. Temperature sensor No. 474120.

### Technical description

Error limit (-30 to 0 °C)	±2 or ±2 % of the measured value °C
Optics	30: 1

Error limit (0.1 to 400 °C)	± 1 or ± 1 % of the measured value °C
Measuring range	-30 - 400 °C
Emission level adjustable	0.1 - 1
Width	38 mm
Length	75 mm
Weight	200 g
Height	190 mm
Infra-red resolution	0.1 °C
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081561 6LR61
Power supply	Battery-powered
Calibration	I5
Type of product	Temperature measuring device

## Services

CalibrationInfra-red temperature measuring tool Type A	027600 A
--	----------

## Accessories

Temperature sensor Type K Type OF	474120 OF
Leather protective cover	474029
Temperature sensor Type K Type EF	474120 EF