



## Humidity and temperature measuring tool, Type: 608H2



### Order data

Order number	474050 608H2
GTIN	4029547000331
Item class	47B

### Description

#### Version:

For exact determination of **humidity, temperature, and dew point**. Insensitive to condensation, maintenance-free. **Min / max display** with Reset function. Can be used free-standing or hung up. Additionally with alert function (flashing light) when limit is exceeded.

#### Application:

Ideal for monitoring room air conditioning.

#### Supplied with:

Supplied with battery No. 081561 size 6LR61 and calibration certificate.

### Technical description

Measuring range dew point td	-40 - 70 °C
Error limit relative humidity	2 %
Temperature measurement range	-10 - 70 °C
Relative humidity measurement range	2 - 98 %
Width	111 mm
Height	90 mm

Error limit dew point td	±0.5 (at 25 °C) °C
Depth	40 mm
Resolution temperature (0 – 50 °C)	0.1 °C
Article no of the battery / rechargeable battery fitted	081561 6LR61
Number of batteries contained	1
Power supply	Battery-powered
Calibration	I6
Type of product	Temperature and humidity measuring device

## Services

CalibrationThermo-hygrometer Type A	027660 A
DAkkS calibrationThermo-hygrometer Type A	027670 A