



Temperature measuring device with temperature stick, Type: T1



Order data

Order number	474080 T1
GTIN	4029547008368
Item class	47B

Description

Version:

Pocket-size mini temperature measuring tool.

High accuracy (thermocouples type K).

Patented pivot head (180°). Temperature stick with immersion / probe sensor for measuring in liquids, soft or powdered substances or in the air.

Supplied with:

Fastening clip, 3 batteries No. 081561 size LR3.

Technical description

Error limit remainder of measurement range	±1 %
Sensor tube length	200 mm
Error limit (-50.0 to 99.9 °C)	±1 °C
Sensor tube Ø	3 mm
Response time t_{99}	10 s
Resolution	0.1 °C

Measurement variables	°C / °F
Measuring range	-50 to +350, up to 500 for short periods °C
Battery life approx.	1000 h
Calibration	I7
Article no of the battery / rechargeable battery fitted	081561 LR3
Number of batteries contained	3
Power supply	Battery-powered
Type of product	Temperature measuring device

Services

Calibration Temperature sensor with / without display Type A	027520 A
---	----------

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------