



## Data logger with USB docking station, Type: 174T



### Order data

Order number	474200 174T
GTIN	4029547010828
Item class	47B

### Description

**Version:**

Handy data logger with display. Internal memory for 16,000 measurement values. High data security, even when the battery is flat.

Measurement interval adjustable between 1 min. and 24 h. Battery life > 1 year (measurement interval 15 min., 25 °C).

USB interface (docking station) permits quick and easy configuration of the logger and uploading the measured data.

**Function:**

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

**Supplied with:**

Wall bracket, 2 batteries No. 081560 size CR2032, manufacturer's certificate of conformity.

Additional docking station with USB connection cable. ComSoft Basic V5 software available for downloading free of charge.

### Technical description

Height	18.5 mm
IP Index of Protection	IP 65

Length	60 mm
Width	38 mm
Error limit temperature	±0.5 °C
Temperature measurement range	-30 - 70 °C
Calibration	I9
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	2
Power supply	Battery-powered
Interface	USB interface
Device memory	16000 measured values
Type of product	Data logger

## Services

CalibrationTemperature measuring device, room temperature Type B	027650 B
DAkkS calibrationThermo-hygrometer Type A	027670 A

## Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------