



## Data logger with USB docking station, Type: 174H



### Order data

|              |               |
|--------------|---------------|
| Order number | 474200 174H   |
| GTIN         | 4029547010835 |
| Item class   | 47B           |

### Description

#### Version:

Handy data logger with display. Internal memory for 16,000 measurement values. High data security, even when the battery is flat.

Measurement interval adjustable between 1 min. and 24 h. Battery life > 1 year (measurement interval 15 min., 25 °C).

USB interface (docking station) permits quick and easy configuration of the logger and uploading the measured data. Additional measurement and logging of the relative humidity.

#### Supplied with:

Wall bracket, 2 batteries No. 081560 size CR2032, manufacturer's certificate of conformity.

Additional docking station with USB connection cable. ComSoft Basic V5 software available for downloading free of charge.

Interface: USB interface

Calibration: I6

Temperature measurement range: -20 - 70 °C

Relative humidity measurement range: 0 - 100 %

Error limit temperature:  $\pm 0.5$  °C

Error limit relative humidity:  $\pm 3$  %

Length: 60 mm

Width: 38 mm

### Technical description

|   |                       |
|---|-----------------------|
| Width   | 38 mm                 |
| Temperature measurement range                           | -20 - 70 °C           |
| Length  | 60 mm                 |
| Error limit relative humidity                           | ±3 %                  |
| Height  | 18.5 mm               |
| Error limit temperature                                 | ±0.5 °C               |
| Calibration   | I6                    |
| Relative humidity measurement range                     | 0 - 100 %             |
| Article no of the battery / rechargeable battery fitted | 081560 CR2032         |
| Number of batteries contained                           | 2                     |
| Power supply  | Battery-powered       |
| Interface   | USB interface         |
| Device memory   | 16000 measured values |
| Type of product   | Data logger           |

## Services

|  |          |
|--|----------|
| Calibration Thermo-hygrometer              | 016900   |
| Labelling laser-etched Type                | 018940   |
| DAkkS calibration Thermo-hygrometer        | 016930   |
| Calibration Thermo-hygrometer Type A       | 027660 A |
| DAkkS calibration Thermo-hygrometer Type A | 027670 A |

## Accessories

|   |               |
|---|---------------|
| Button cell / special battery Battery type CR2032 | 081560 CR2032 |
|---|---------------|