



Temperature measuring device without measuring sensor, Type: 925



Order data

Order number	474110 925
GTIN	4029547003592
Item class	47B

Description

Version:

Sturdy "All-round" temperature measuring device. Simple handling for daily routine work.

Supplied with:

Including 1 battery No. 081561 size 6LR61 and test certificate (without measuring sensor).

Calibration: I8

Measuring range temperature (sensor type K): -50 - 1000 °C

Resolution: 0.1 / 1 (from +200) °C

Error limit: $\pm 0.5 + 0.3 \%$ of the measured value (for -40 to 900 °C) $\pm 0.7 + 0.5 \%$ of the measured value (remainder of the measurement range) °C

Length: 182 mm

Width: 65 mm

Height: 40 mm

Technical description

Width	65 mm
Length	182 mm

Resolution	0.1 / 1 (from +200) °C
Measuring range temperature (sensor type K)	-50 - 1000 °C
Height	40 mm
Manufacturer's designation	925
Error limit	±0.5 +0.3 % of the measured value (for -40 to 900 °C) ±0.7 +0.5 % of the measured value (remainder of the measurement range) °C
Article no of the battery / rechargeable battery fitted	081561 6LR61
Number of batteries contained	1
Power supply	Battery-powered
Calibration	I8
Type of product	Temperature measuring device

Services

Calibration Temperature display unit Number of inlets 1	016820 1
Labelling laser-etched Type	018940
DAkkS calibration Temperature display unit Number of inlets 1	016840 1
Recalibration Temperature display unit Number of inlets 1	027500 1
DAkkS calibration Calibration temperature display unit Number of inlets 1	027510 1

Accessories

Top Safe "protective hood" for No. 474110	474112
Temperature sensor Type K Type EF	474120 EF
Temperature sensor Type K Type OF	474120 OF
Alkaline-manganese batteries International size 6LR61	081556 6LR61