



## Data logger without USB docking station, Type: 174T



### Order data

Order number	474201 174T
GTIN	4029547010798
Item class	47B

### Description

#### Version:

Handy data logger with display. Internal memory for 16,000 measurement values. High data security, even when the battery is flat.

Measurement interval adjustable between 1 min. and 24 h. Battery life > 1 year (measurement interval 15 min., 25 °C).

USB interface (docking station) permits quick and easy configuration of the logger and uploading the measured data.

#### Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

#### Supplied with:

Wall bracket, 2 batteries No. 081560 size CR2032, manufacturer's certificate of conformity.

### Technical description

IP Index of Protection	IP 65
Length	60 mm

Width	38 mm
Height	18.5 mm
Error limit temperature	±0.5 °C
Temperature measurement range	-30 - 70 °C
Calibration	I9
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081560 CR2032
Power supply	Battery-powered
Device memory	16000
Type of product	Data logger

## Services

DAkkS calibrationThermo-hygrometer Type A	027670 A
CalibrationTemperature measuring device, room temperature Type B	027650 B

## Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------