



## Data logger without USB docking station, Type: 174H



### Order data

Order number	474201 174H
GTIN	4029547010804
Item class	47B

### Description

#### Version:

Handy data logger with display. Internal memory for 16,000 measurement values. High data security, even when the battery is flat.

Measurement interval adjustable between 1 min. and 24 h. Battery life > 1 year (measurement interval 15 min., 25 °C).

USB interface (docking station) permits quick and easy configuration of the logger and uploading the measured data. Additional measurement and logging of the relative humidity.

#### Supplied with:

Wall bracket, 2 batteries No. 081560 size CR2032, manufacturer's certificate of conformity.

### Technical description

Temperature measurement range	-20 - 70 °C
Error limit relative humidity	±3 %
Error limit temperature	±0.5 °C
Length	60 mm

Width	38 mm
Height	18.5 mm
Calibration	I6
Article no of the battery / rechargeable battery fitted	081560 CR2032
Number of batteries contained	2
Power supply	Battery-powered
Device memory	16000
Type of product	Data logger

### Services

CalibrationThermo-hygrometer Type A	027660 A
DAkkS calibrationThermo-hygrometer Type A	027670 A

### Accessories

Button cell / special battery Battery type CR2032	081560 CR2032
---	---------------