



Depth gauge with analogue dial indicator, Measuring range: 30mm



Order data

Order number	434805 30
GTIN	4031452161892
Item class	42C

Description

Version:

Hardened base with fine lapped contact surface. Dial indicator securely clamped by collet. **Dial indicator with anticlockwise scale measuring depth can be read off directly.** Greater depths can be measured using extension rods of differing lengths(see No. 434920).

Supplied with:

Dial indicator No. 434807 size 10 or 30.

Optional extras:

Extension for No. 434920.

Technical description

Calibration	C1
Calibration	C8
Bridge length	80 mm
Reading per pointer revolution	1 mm
Bridge width	16 mm

Measuring range	30 mm
Probe plunger Ø	5 mm
Dial indicator Ø	58 mm
Graduation	0.01 mm
Measurement variation E MPE (measurement range)	20 µm
Standard	Manufacturer's standard
Measurement technology	analogue
Packaging	sturdy box
Type of product	Depth gauge

Services

CalibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 30 mm	023000 30
DAkkS calibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 100 mm	023010 100
CalibrationMeasurement head Type B	023360 B

Accessories

Extension for contact points Length L 70 mm	434920 70
Extension for contact points Length L 80 mm	434920 80
Extension for contact points Length L 50 mm	434920 50
Dial indicator with anticlockwise scale Measuring range 30 mm	434807 30
Extension for contact points Length L 60 mm	434920 60
Extension for contact points Length L 30 mm	434920 30
Extension for contact points Length L 100 mm	434920 100
Extension for contact points Length L 40 mm	434920 40
Knurled nut Thread M14X0,5	434806 M14X0,5
Extension for contact points Length L 90 mm	434920 90
Extension for contact points Length L 10 mm	434920 10

Extension for contact points Length L 20 mm	434920 20
Extension for contact points Length L 15 mm	434920 15