



Air and infrared temperature measuring device, Type: 810



Order data

Order number	474260 810
GTIN	4029547008320
Item class	47B

Description

Version:

Handy device, easy to operate, high quality sensors with long-term stability. Hold function, min / max memory and display illumination for ease of reading the measurement values.

Supplied with:

Supplied with protective cap, belt bag and 2 batteries No. 081561 size LR3.

Calibration: I9

Measuring range air: -10 - 50 °C

Measuring range infra-red: -30 - 300 °C

Error limit infra-red: ± 2 °C

Error limit air: ± 0.5 °C

Optics: 6: 1

Length: 119 mm

Technical description

Error limit infra-red	± 2 °C
Optics	6: 1

Length	119 mm
Width	46 mm
Measuring range infra-red	-30 - 300 °C
Height	25 mm
Error limit air	±0.5 °C
Measuring range air	-10 - 50 °C
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081561 LR3
Power supply	Battery-powered
Calibration	I5
Calibration	I9
Type of product	Temperature measuring device

Services

Calibration Infra-red temperature measuring tool Type A	016730 A
Labelling laser-etched Type	018940
DAkkS calibration Infra-red temperature measuring tool Type A	016890 A
Calibration Temperature measuring device, room temperature Type B	016920 B
DAkkS calibration Thermo-hygrometer	016930
DAkkS calibration Thermo-hygrometer Type A	027670 A
DAkkS calibration Infra-red temperature measuring tool Type A	027610 A
Calibration Temperature measuring device, room temperature Type B	027650 B
Calibration Infra-red temperature measuring tool Type A	027600 A

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------

Alkaline-manganese batteries International size LR3

081556 LR3