



Dial indicator with anticlockwise scale, Measuring range: 10mm



Order data

Order number	434807 10
GTIN	4031452160758
Item class	46C

Description

Version:

Precision dial indicator with metal housing, clamping shank \varnothing 8 mm h6, hardened and ground. With **anticlockwise scale** for use with depth gauge bases and precision bore gauges.

Suitable for:

Depth gauges No. 434805 Internal precision bore gauges No. 435190; 435192; 435040; 435050; 435060; 435070; 435010; 435110; 435120; 435154; 435155; 435156; 435157; 435158; 435159 and 435125.

Technical description

Graduation	0.01 mm
Measuring range	0 - 10 mm
Body \varnothing	57 mm
Gauging force	0.7 - 1.4 N
Calibration	C1
Reading per pointer revolution	1 mm

Standard	Manufacturer's standard
Dial indicator Ø	58 mm
Probe plunger Ø	4 mm
Measurement variation MPE (measurement range)	15 µm
Measurement technology	analogue
Packaging	sturdy box
Type of product	dial gauge

Services

DAkkS calibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 12,5 mm	023010 12,5
CalibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 10 mm	023000 10

Accessories

Dial indicator glass Type 40	432010 40
------------------------------	-----------