



## DS double-ended grinding machine, 400 V, Type: DS12/250



### Order data

Order number	077512 DS12/250
GTIN	2050001673947
Item class	03S

### Description

#### Version:

The **extremely smooth-running** motor ensures a long working life, even when run **continuously. Supplied without grinding wheels.**

Exceptionally robust three-phase double-ended bench grinding machines, bench-top type. Sturdy workpiece supports, restart inhibit, and eye protection shields ensure user safety.

#### Note:

Suitable grinding wheels can be found from No. 596100.

### Technical description

Manufacturer's designation	DS12/250
maximum speed	1450 min <sup>-1</sup>
Power consumption	730 W
Weight	47 kg
Abrasive disc width T	32 mm
Abrasive disc hole Ø H	51 mm
Abrasive disc Ø D	250 mm
Power supply	Mains operated
Type of product	Double grinding machine

## Accessories

Bench grinding wheel D×T×H (mm) Type EK60	596400 EK60
Support stand suitable for machine DS12	077513 DS12
Bench grinding wheel D×T×H (mm) Type NK36	596510 NK36
Bench grinding wheel D×T×H (mm) Type NK60	596400 NK60
Tool mounting plate left-hand Type AT1	077519 AT1
Bench grinding wheel D×T×H (mm) Type EK60	596510 EK60
Bench grinding wheel D×T×H (mm) Type EK60	596220 EK60
Bench grinding wheel D×T×H (mm) Type NK60	596350 NK60
Bench grinding wheel D×T×H (mm) Type SC80	596400 SC80
Bench grinding wheel D×T×H (mm) Type EK80	596220 EK80
Bench grinding wheel D×T×H (mm) Type SC80	596220 SC80
Bench grinding wheel D×T×H (mm) Type SC80	596510 SC80
Bench grinding wheel D×T×H (mm) Type EK60	596350 EK60
Eye protection shield for No. 077502 Type DS1	077509 DS1
Bench grinding wheel D×T×H (mm) Type EK80	596350 EK80
Bench grinding wheel D×T×H (mm) Type EK80	596510 EK80
Bench grinding wheel D×T×H (mm) Type NK60	596220 NK60
Tool mounting plate right-hand Type AT1	077525 AT1
Bench grinding wheel D×T×H (mm) Type C800	596350 C800
Bench grinding wheel D×T×H (mm) Type SC80	596350 SC80
Bench grinding wheel D×T×H (mm) Type NK60	596510 NK60
Bench grinding wheel D×T×H (mm) Type NK36	596350 NK36