



Materials humidity measuring device, Type: 606-2



Order data

Order number	474262 606-2
GTIN	4029547008306
Item class	47B

Description

Application:

Precise measurement of the material moisture content using stored characteristic curves for various types of wood (such as beech, fir, oak. . .) and various building materials (such as concrete, tiles, plaster. . .). Additional measurement of temperature and relative humidity of ambient air (dewpoint calculation).

Technical description

Error limit temperature	± 0.5 °C
Calibration	I6
Temperature measurement range	-10 - 50 °C
Length	119 mm
Relative humidity measurement range	0 - 55 %
Height	25 mm
Error limit relative humidity	± 1 %

Width	46 mm
Number of batteries contained	2
Article no of the battery / rechargeable battery fitted	081561 LR3
Power supply	Battery-powered
Type of product	Material moisture meter

Services

CalibrationThermo-hygrometer Type A	027660 A
DAkkS calibrationThermo-hygrometer Type A	027670 A

Accessories

Alkaline-manganese batteries International size LR3	081561 LR3
---	------------