



Dial indicator with anticlockwise scale, Measuring range: 30mm



Order data

Order number	434807 30
GTIN	4031452160765
Item class	46C

Description

Version:

Precision dial indicator with metal housing, clamping shank \varnothing 8 mm h6, hardened and ground. With **anticlockwise scale** for use with depth gauge bases and precision bore gauges.

Suitable for:

Depth gauges No. 434805

Technical description

Graduation	0.01 mm
Reading per pointer revolution	1 mm
Body \varnothing	57 mm
Calibration	C1
Gauging force	0.8 - 1.6 N
Measuring range	0 - 30 mm
Standard	Manufacturer's standard

Probe plunger Ø	5 mm
Dial indicator Ø	58 mm
Measurement variation MPE (measurement range)	20 µm
Measurement technology	analogue
Packaging	sturdy box
Type of product	dial gauge

Services

DAkkS calibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 100 mm	023010 100
CalibrationDial indicator analogue 0.01 and digital 0.01 / 0.001 maximum measuring span 30 mm	023000 30

Accessories

Dial indicator glass Type 58	432010 58
------------------------------	-----------