



High-performance coolant concentrate Plus, Contents: 200l



Order data

Order number	084260 200
GTIN	2050000967344
Item class	08J

Description

Version:

Cooling lubricant for **demanding applications, free of hydrochlorous acid, formaldehyde and boric acid**. High-pressure additives prevent displacement of the lubricating film; it remains on the cutting tool in molecular concentrations even under the most severe loading. High performance coolant concentrate for the **most difficult high tensile materials** and difficult aluminium alloys and non-ferrous metals, free of amines.

Advantage:

Improves **tool-life, cutting performance** and **surface quality**. **Chlorine-free** - releases no hazardous vapours, **non-polluting**.

Concentrates **protect against rust**, do not attack paintwork, and are **physiologically harmless**, as well as very **resistant to bacterial contamination**, and kind to the skin.

Application:

Multi-purpose for **all machining operations** (turning, milling, drilling, tapping, reaming, broaching, **sawing**, grinding). Indispensable when machining difficult materials. Normal **mixing ratio 1: 20**, for high-tensile materials and stainless steel mixing ratio 1: 10 to 1: 15.

Note:

Jokisch slide oils and machine bed oils are available on request. These are perfectly compatible with all other Jokisch products (no sticky residues) and can also be used as hydraulic and gear oils.

Version: Barrel

Contents: 200 l

Technical description

Colour	pale brown
Version	Barrel
Kinematic viscosity	93 mm ² /s
Storage temperature	5 - 40 °C
Contents	200 l
Type of product	Cooling lubricant

Accessories

Barrel pump	084355
-------------	--------