

Garant
Compact clamp, Type: 47

Order data

Order number	370142 47
GTIN	4045197602497
Item class	31L

Description
Version:

Body and pressure arm of hardened stainless steel, with high load capacity. The pressure piece swings on a sprung ball and can quickly be exchanged without using any tools. Special nylon seal provides protection against the ingress of dirt.

Advantage:

Compact design, approx. 30 % smaller than comparable models. Time-saving automatic clamping and releasing.

Standard DIN 912 socket head screws (M10 / M12) can be used.

Optional extras:

No. 370350 clamping wrench, No. 370430 pressure pieces.

Clamping height S: -1 - 90 mm

Length L: 95 mm

Width B: 35 mm

Height H: 81 mm

Pressure arm r: 75 mm

maximum clamping force: 16 kN

Technical description

maximum clamping force	16 kN
------------------------	-------

Pressure arm r	75 mm
Reach A	47 mm
Clamping height S	-1 - 90 mm
Tapped hole for socket-head screws DIN 912	M10 / M12
Height H	81 mm
Width B	35 mm
Length L	95 mm
maximum torque	105 N·m
Type of product	Compact clamp

Accessories

Riser block for compact clamps Type 80	370145 80
Clamping wrench 11 AF for Monobloc, Duo, and chain clamping tool	370350
Swivel shoe Type-No. 5	370430 5
Swivel shoe Type-No. 1	370430 1
Swivel shoe Type-No. 2	370430 2
Swivel shoe Type-No. 4	370430 4
Swivel shoe Type-No. 3	370430 3
Riser blocks for compact clamps Height H 80 mm	370146 80