

**Garant**
**Compact clamp, Type: 67**

**Order data**

Order number	370142 67
GTIN	4045197605900
Item class	31L

**Description**
**Version:**

Body and pressure arm of hardened stainless steel, with high load capacity. The pressure piece swings on a sprung ball and can quickly be exchanged without using any tools. Special nylon seal provides protection against the ingress of dirt.

**Advantage:**

Compact design, approx. 30 % smaller than comparable models. Time-saving automatic clamping and releasing.

Standard DIN 912 socket head screws (M10 / M12) can be used.

**Optional extras:**

No. 370350 clamping wrench, No. 370430 pressure pieces.

Clamping height S: -8 - 100 mm

Length L: 95 mm

Width B: 35 mm

Height H: 81 mm

Pressure arm r: 94 mm

maximum clamping force: 12 kN

**Technical description**

Clamping height S	-8 - 100 mm
-------------------	-------------

Reach A	67 mm
Tapped hole for socket-head screws DIN 912	M10 / M12
Pressure arm r	94 mm
maximum clamping force	12 kN
Height H	81 mm
Width B	35 mm
Length L	95 mm
maximum torque	105 N·m
Type of product	Compact clamp

---

## Accessories

Clamping wrench 11 AF for Monobloc, Duo, and chain clamping tool	370350
Swivel shoe Type-No. 1	370430 1
Swivel shoe Type-No. 5	370430 5
Swivel shoe Type-No. 4	370430 4
Riser blocks for compact clamps Height H 80 mm	370146 80
Swivel shoe Type-No. 2	370430 2
Riser block for compact clamps Type 80	370145 80
Swivel shoe Type-No. 3	370430 3