



## Feeler gauge shim strip set In a wall rack, Type: 0,01-0,25



### Order data

Order number	478440 0,01-0,25
GTIN	4045197524256
Item class	42H

### Description

**Version:**

15-piece set in a metal wall rack. Feeler gauges in plastic boxes.

**Content:**

1 each feeler gauge shim roll No. 478502: 0.01 to 0.1 (0.01 increments) 0.12; 0.15; 0.18; 0.20; 0.25

**Supplied with:**

Fastening material and feeler gauge holder No. 478510.

### Technical description

Height	110 mm
Length	330 mm
Depth	100 mm
Standard	Works standard
Type of product	Feeler gauge shim strip

### Accessories

Feeler gauge shim roll 12.7 mm×5 m Thickness 0,02 mm	478502 0,02
--	-------------

Feeler gauge shim roll 12.7 mm×5 m Thickness 0,2 mm	478502 0,2
Feeler gauge shim roll 12.7 mm×5 m Thickness 0,08 mm	478502 0,08
Feeler gauge shim roll 12.7 mm×5 m Thickness 0,07 mm	478502 0,07
Feeler gauge shim roll 12.7 mm×5 m Thickness 0,15 mm	478502 0,15
Feeler gauge shim roll 12.7 mm×5 m Thickness 0,25 mm	478502 0,25
Feeler gauge holder	478510
Feeler gauge shim roll 12.7 mm×5 m Thickness 0,18 mm	478502 0,18
Feeler gauge shim roll 12.7 mm×5 m Thickness 0,1 mm	478502 0,1
Feeler gauge shim roll 12.7 mm×5 m Thickness 0,05 mm	478502 0,05
Feeler gauge shim roll 12.7 mm×5 m Thickness 0,04 mm	478502 0,04
Feeler gauge shim roll 12.7 mm×5 m Thickness 0,03 mm	478502 0,03
Feeler gauge shim roll 12.7 mm×5 m Thickness 0,01 mm	478502 0,01
Feeler gauge shim roll 12.7 mm×5 m Thickness 0,09 mm	478502 0,09
Feeler gauge shim roll 12.7 mm×5 m Thickness 0,12 mm	478502 0,12
Feeler gauge shim roll 12.7 mm×5 m Thickness 0,06 mm	478502 0,06