



## Feeler gauge shim roll 12.7 mm×5 m, Carbon steel, Thickness: 0,9mm



### Order data

|              |               |
|--------------|---------------|
| Order number | 478450 0,9    |
| GTIN         | 2050001055149 |
| Item class   | 48B           |

### Description

#### Version:

Cold rolled, hard spring feeler strip steel of maximum precision. From size 0.02, the strip thickness is continuously marked and cannot be wiped off (exception: for No. 478502 from size 0.08).

Stored in a practical dispenser; pull out like a tape measure. The desired length can be cut from the 5 or 10 m long strip.

**C-steel** – Carbon steel, material No. 1.1274, cold rolled, hardened, bright surface. **(size 0.01 and 0.02 stainless).**

#### Application:

In jig and tool building for aligning and adjusting machine parts, as a shim for aligning components, for tolerance measurements of all kinds, for checking fits and guides, for setting up printing rollers.

### Technical description

|             |        |
|-------------|--------|
| Thickness   | 0.9 mm |
| Error limit | ±13 µm |

|                 |                         |
|-----------------|-------------------------|
| Standard        | Works standard          |
| Tolerance       | T3                      |
| Material        | Carbon steel            |
| Roll length     | 5 m                     |
| Roll width      | 12.7 mm                 |
| Type of product | Feeler gauge shim strip |