



Tapered clamp with adjusting support screw, Slot width a: 12mm



Order data

Order number	370680 12
GTIN	4020772070274
Item class	35A

Description

Version:

Clamp painted. Clamping height steplessly adjustable via screw (without clamping lever).

Material:

Quenched and tempered steel, screw strength 8.8 or 10.9 (depending on size).

Supplied with:

Adjusting screw and T-bolt DIN 787 (No. 375300).

Technical description

Slot width a	12 mm
Slot length f	40 mm
Distance from tip to slot	21 mm
Tee bolt DIN 787, No. 375300	Size 1212100
Clamping height h	10 - 40 mm
Length L	100 mm

Width B	40 mm
Height H	20 mm
Type	6314V
Type of product	Plain clamp

Accessories

Detent clamp lever Slot width a 12 mm	370750 12
---------------------------------------	-----------