

**Tapered clamp with adjusting support screw, Slot width a: 16mm****Order data**

Order number	370680 16
GTIN	4020772070298
Item class	35A

**Description****Version:**

Clamp painted. Clamping height steplessly adjustable via screw (without clamping lever).

**Material:**

Quenched and tempered steel, screw strength 8.8 or 10.9 (depending on size).

**Supplied with:**

Adjusting screw and T-bolt DIN 787 (No. 375300).

**Technical description**

Slot length f	45 mm
Slot width a	16 mm
Tee bolt DIN 787, No. 375300	Size 1616125
Distance from tip to slot	26 mm
Clamping height h	13 - 48 mm
Length L	125 mm

Width B	50 mm
Height H	25 mm
Type	6314V
Type of product	Plain clamp

---

## Accessories

Detent clamp lever Slot width a 16 mm	370750 16
---------------------------------------	-----------