

## MT drill chuck arbor, precision version, MT / drill chuck taper: 2/18



### Order data

Order number	342600 2/18
GTIN	4045197308580
Item class	33A

### Description

#### Version:

**Through hardened and ground.** High long-term concentricity because swarf cannot be pressed into the hardened surface and no notches can occur from minor impacts.

With MT shank and tang.

The **high precision version** offers maximum concentricity and is recommended for self-tightening high-performance drill chucks No. 341000. Shanks also suitable for drill chuck taper B18 (taper  $\varnothing$  17.431 mm): Drill chucks No. 341000, 341010 and 341250.

#### Application:

For mounting drill chucks on drills, lathes, jig borers etc.

#### Standard:

Bohrfutterkegel **DIN 238**.

### Technical description

Morse taper MT size	2
Drill chuck taper DIN 238	B 18
Taper $\varnothing$ D	17.78 mm
Type of product	Drill chuck adapter