



Tapered clamp with adjusting support screw, Slot width a: 22mm



Order data

Order number	370680 22
GTIN	4020772070311
Item class	35A

Description

Version:

Clamp painted. Clamping height steplessly adjustable via screw (without clamping lever).

Material:

Quenched and tempered steel, screw strength 8.8 or 10.9 (depending on size).

Supplied with:

Adjusting screw and T-bolt DIN 787 (No. 375300).

Technical description

Slot width a	22 mm
Distance from tip to slot	30 mm
Tee bolt DIN 787, No. 375300	Size 2220160
Slot length f	60 mm
Clamping height h	16 - 65 mm
Length L	160 mm

Width B	60 mm
Height H	30 mm
Type	6314V
Type of product	Plain clamp