

## MT drill chuck arbor, precision version, MT / drill chuck taper: 1/12



### Order data

Order number	342600 1/12
GTIN	4045197308528
Item class	33A

### Description

#### Version:

**Through hardened and ground.** High long-term concentricity because swarf cannot be pressed into the hardened surface and no notches can occur from minor impacts.

With MT shank and tang.

The **high precision version** offers maximum concentricity and is recommended for self-tightening high-performance drill chucks No. 341000.

#### Application:

For mounting drill chucks on drills, lathes, jig borers etc.

#### Standard:

Bohrfutterkegel **DIN 238**.

### Technical description

Morse taper MT size	1
Taper $\varnothing$ D	12.065 mm
Drill chuck taper DIN 238	B 12
Type of product	Drill chuck adapter