

**Morse taper arbor with locking thread, MT / drill chuck taper: 2/12****Order data**

| | |
|--------------|---------------|
| Order number | 342700 2/12 |
| GTIN | 4045197294920 |
| Item class | 32X |

Description**Version:**

Through hardened and ground. High long-term concentricity because swarf cannot be pressed into the hardened surface and no notches can occur from minor impacts.

High precision version with MT shank and internal locking thread.

Application:

For mounting drill chucks on milling machines with Morse tapers.

Standard:

Bohrfutterkegel **DIN 238**.

Technical description

| | |
|---------------------------|---------------------|
| Taper \varnothing D | 12.065 mm |
| Morse taper MT size | 2 |
| Internal pull thread | M10 |
| Drill chuck taper DIN 238 | B 12 |
| Type of product | Drill chuck adapter |