

**Tapered clamp with adjusting support screw offset, Slot width a: 22mm****Order data**

Order number	370685 22
GTIN	4020772074661
Item class	35A

Description**Version:**

Quenched and tempered steel, painted, screw strength 8.8.

Application:

To achieve the **lowest clamping height, turn the clamp around.**

Supplied with:

Adjusting screw and T-bolt DIN 787 (No. 375300).

Technical description

Shoulder height A_1	12 mm
Tee bolt DIN 787, No. 375300	Size 2220160
Slot length f	60 mm
Shoulder depth A_2	15 mm
Slot width a	22 mm
Distance from tip to slot	30 mm

Clamping height h	16 - 77 mm
Length L	160 mm
Width B	60 mm
Height H	30 mm
Type	6314AV
Type of product	Plain clamp