



Tapered clamp with adjusting support screw offset, Slot width a: 14mm



Order data

Order number	370685 14
GTIN	4020772074623
Item class	35A

Description

Version:

Quenched and tempered steel, painted, screw strength 8.8.

Application:

To achieve the **lowest clamping height, turn the clamp around.**

Supplied with:

Adjusting screw and T-bolt DIN 787 (No. 375300).

Technical description

Slot width a	14 mm
Shoulder depth A ₂	10 mm
Tee bolt DIN 787, No. 375300	Size 1412100
Shoulder height A ₁	8 mm
Distance from tip to slot	21 mm
Slot length f	40 mm

Clamping height h	10 - 46 mm
Length L	100 mm
Width B	40 mm
Height H	20 mm
Type	6314AV
Type of product	Plain clamp

Accessories

Detent clamp lever Slot width a 12 mm	370750 12
---------------------------------------	-----------