



Cranked clamp with adjusting support screw, Slot width a: 10mm



Order data

Order number	370720 10
GTIN	4020772071271
Item class	35A

Description

Version:

Clamp painted. Clamping height steplessly adjustable via screw (without clamping lever).

Material:

Quenched and tempered steel, screw strength 8.8 or 10.9 (depending on size!).

Supplied with:

Adjusting screw and T-bolt DIN 787 (No. 375300).

Technical description

Slot length f	32 mm
Slot width a	10 mm
Distance from tip to slot	36 mm
Tee bolt DIN 787, No. 375300	Size 101080
Clamping height h	22 - 46 mm
Height H	15 mm
Length L	100 mm

Width B	11 mm
Type	6316V
Type of product	Plain clamp