



Tapered clamp with adjusting support screw offset, Slot width a: 16mm



Order data

Order number	370685 16
GTIN	4020772074630
Item class	35A

Description

Version:

Quenched and tempered steel, painted, screw strength 8.8.

Application:

To achieve the **lowest clamping height, turn the clamp around.**

Supplied with:

Adjusting screw and T-bolt DIN 787 (No. 375300).

Technical description

Distance from tip to slot	26 mm
Shoulder height A ₁	10 mm
Tee bolt DIN 787, No. 375300	Size 1616125
Slot width a	16 mm
Shoulder depth A ₂	12.5 mm
Slot length f	45 mm

Clamping height h	13 - 58 mm
Length L	125 mm
Width B	50 mm
Height H	25 mm
Type	6314AV
Type of product	Plain clamp

Accessories

Detent clamp lever Slot width a 16 mm	370750 16
---------------------------------------	-----------