

**Cranked clamp with adjusting support screw, Slot width a: 12mm****Order data**

Order number	370720 12
GTIN	4020772071288
Item class	35A

Description**Version:**

Clamp painted. Clamping height steplessly adjustable via screw (without clamping lever).

Material:

Quenched and tempered steel, screw strength 8.8 or 10.9 (depending on size!).

Supplied with:

Adjusting screw and T-bolt DIN 787 (No. 375300).

Technical description

Distance from tip to slot	44 mm
Slot length f	40 mm
Slot width a	12 mm
Tee bolt DIN 787, No. 375300	Size 1212100
Clamping height h	28 - 58 mm
Height H	20 mm
Length L	125 mm

Width B	14 mm
Type	6316V
Type of product	Plain clamp