

**Tapered clamp with adjusting support screw offset, Slot width a: 18mm****Order data**

Order number	370685 18
GTIN	4020772074647
Item class	35A

**Description****Version:**

Quenched and tempered steel, painted, screw strength 8.8.

**Application:**

To achieve the **lowest clamping height, turn the clamp around.**

**Supplied with:**

Adjusting screw and T-bolt DIN 787 (No. 375300).

**Technical description**

Shoulder depth $A_2$	12.5 mm
Slot length f	45 mm
Tee bolt DIN 787, No. 375300	Size 1816125
Shoulder height $A_1$	10 mm
Distance from tip to slot	26 mm
Slot width a	18 mm

Clamping height h	13 - 56 mm
Length L	125 mm
Height H	25 mm
Width B	50 mm
Type	6314AV
Type of product	Plain clamp

---

## Accessories

Detent clamp lever Slot width a 16 mm	370750 16
---------------------------------------	-----------