

**Steplessly adjustable clamp, Slot width a: 12mm****Order data**

Order number	370660 12
GTIN	4020772074906
Item class	35A

**Description****Version:**

The clamp and Tee bolt form a single unit (no loose parts). The shape of the clamp provides for infinitely variable adjustment without additional blocks.

**Application:**

For quick and reliable clamping of various component heights on milling machines.

**Material:**

Quenched and tempered steel, galvanised, screw strength 8.8 or 10.9 (depending on size!).

**Supplied with:**

T-bolt DIN 787 (No. 375300).

**Technical description**

Tee bolt DIN 787, No. 375300	Size 1212125
Slot width a	12 mm
Clamping height h	0 - 50 mm
Length L	140 mm

Width B	50 mm
Type	6321
Type of product	Clamp

---

## Accessories

Detent clamp lever Slot width a 12 mm	370750 12
---------------------------------------	-----------