



Tapered clamp with adjusting support screw offset, Slot width a: 20mm



Order data

Order number	370685 20
GTIN	4020772074654
Item class	35A

Description

Version:

Quenched and tempered steel, painted, screw strength 8.8.

Application:

To achieve the **lowest clamping height, turn the clamp around.**

Supplied with:

Adjusting screw and T-bolt DIN 787 (No. 375300).

Technical description

Slot width a	20 mm
Shoulder depth A ₂	15 mm
Shoulder height A ₁	12 mm
Slot length f	60 mm
Tee bolt DIN 787, No. 375300	Size 2020160
Distance from tip to slot	30 mm

Clamping height h	16 - 77 mm
Length L	160 mm
Height H	30 mm
Width B	60 mm
Type	6314AV
Type of product	Plain clamp