

MT drill chuck arbor, precision version, MT / drill chuck taper: 4/16



Order data

Order number	342600 4/16
GTIN	4045197308641
Item class	33A

Description

Version:

Through hardened and ground. High long-term concentricity because swarf cannot be pressed into the hardened surface and no notches can occur from minor impacts.

With MT shank and tang.

The **high precision version** offers maximum concentricity and is recommended for self-tightening high-performance drill chucks No. 341000.

Application:

For mounting drill chucks on drills, lathes, jig borers etc.

Standard:

Bohrfutterkegel **DIN 238**.

Technical description

Morse taper MT size	4
Drill chuck taper DIN 238	B 16
Taper \varnothing D	15.733 mm
Type of product	Drill chuck adapter