

Kroepelin
Längenmesstechnik

Digital internal quick caliper, Measuring range: 2,5-12,5 mm



Order data

Order number	438974 2,5-12,5
GTIN	2050001055187
Item class	46Q

Description

Version:

1 fixed and 1 movable arm with carbide spherical contact points. **Digital display of the absolute value.**

By entering **preset values**, variations can be determined against any value.

Supplied with:

1 battery No. 081556 size LR3, operating instructions.

Optional extras:

Data cable adapter No. 498954 size A2, data cable No. 497440.

Norm: Manufacturer's standard

Reversible reading: mm / inch

Interface: USB interface

Interface: Digimatic interface

IP Index of Protection: IP 67

Measured value saving: Once-off setting of the zero position

Graduations: 0.005 mm

Error limit: 0.015 mm

Repetition accuracy: 0.005 mm

Radius of the blade: 0.1 mm

minimum groove width: 0.4 mm

maximum groove depth: 0.7 mm

Technical description

minimum groove width	0.4 mm
Measuring range	2.5 - 12.5 mm
Graduations	0.005 mm
maximum contact point length L (measurement depth)	12 mm
maximum groove depth	0.7 mm
Radius of the blade	0.1 mm
Repetition accuracy	0.005 mm
Gauging force	0.8 - 1.2 N
Error limit	0.015 mm
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081561 LR3
Norm	Manufacturer's standard
Reversible reading	mm / inch
Interface	USB interface
Interface	Digimatic interface
IP Index of Protection	IP 67
Measured value saving	Once-off setting of the zero position
Measurement technology	digital
Calibration	C7
Type of product	Internal quick calipers

Services

Calibration External / internal quick caliper	013850
Labelling laser-etched Type	018940
DAkkS calibration External / internal quick caliper	011320

Accessories

Connecting cable Type D2	497440 D2
Multi-receiver / USB keyboard interface	498975

Transmitter Type S2	498966 S2
Connecting cable Type D1	497440 D1
Receiver / USB keyboard interface	498965
Connecting cable Type USB2	497440 USB2
Alkaline-manganese batteries International size LR3	081556 LR3
Interface adapter Type A2	498954 A2