

Kroeplin
Längenmesstechnik**Internal quick caliper, Measuring range: 10-30mm****Order data**

Order number	438950 10-30
GTIN	2050001036841
Item class	46Q

Description**Version:**

1 fixed and 1 movable arm with carbide spherical contact points. The deflection of the moving contact point is transmitted to the dial indicator. The measured result can be read directly.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Technical description

Scale divisions	0.01 mm
maximum groove depth	5.2 mm
maximum contact point length L (measurement depth)	80 mm
Measuring range	10 - 30 mm
Carbide spherical point Ø	1 mm
minimum groove width	1.5 mm
Error limit	0.03 mm
Dial indicator Ø	65 mm
Calibration	C7
IP Index of Protection	IP 65

Standard	Manufacturer's standard
Measurement technology	analogue
Type of product	Internal quick caliper

Services

CalibrationExternal / internal quick caliper Type S	023450 S
DAkkS calibrationExternal / internal quick caliper Type S	023460 S