

**Cranked clamp with adjusting support screw, Slot width a: 22mm****Order data**

Order number	370720 22
GTIN	4020772071325
Item class	35A

Description**Version:**

Clamp painted. Clamping height steplessly adjustable via screw (without clamping lever).

Material:

Quenched and tempered steel, screw strength 8.8 or 10.9 (depending on size!).

Supplied with:

Adjusting screw and T-bolt DIN 787 (No. 375300).

Technical description

Tee bolt DIN 787, No. 375300	Size 2220160
Slot width a	22 mm
Slot length f	70 mm
Distance from tip to slot	59 mm
Clamping height h	43 - 92 mm
Height H	30 mm
Length L	200 mm

Width B	22 mm
Type	6316V
Type of product	Plain clamp