

**Kroepelin**  
Längenmesstechnik

## Digital internal quick caliper, Measuring range: 5-15 mm



### Order data

Order number	438974 5-15
GTIN	2050001661609
Item class	46Q

### Description

#### Version:

1 fixed and 1 movable arm with carbide spherical contact points. **Digital display of the absolute value.**

By entering **preset values**, variations can be determined against any value.

#### Supplied with:

1 battery No. 081556 size LR3, operating instructions.

#### Optional extras:

Data cable adapter No. 498954 size A2, data cable No. 497440.

Norm: Manufacturer's standard

Reversible reading: mm / inch

Interface: USB interface

Interface: Digimatic interface

IP Index of Protection: IP 67

Measured value saving: Once-off setting of the zero position

Graduations: 0.005 mm

Error limit: 0.015 mm

Repetition accuracy: 0.005 mm

Carbide spherical point  $\varnothing$ : 0.6 mm

minimum groove width: 0.8 mm

maximum groove depth: 2.3 mm

### Technical description

minimum groove width	0.8 mm
Carbide spherical point Ø	0.6 mm
Gauging force	0.8 - 1.2 N
maximum groove depth	2.3 mm
Repetition accuracy	0.005 mm
Measuring range	5 - 15 mm
Graduations	0.005 mm
maximum contact point length L (measurement depth)	35 mm
Error limit	0.015 mm
Number of batteries contained	1
Article no of the battery / rechargeable battery fitted	081561 LR3
Norm	Manufacturer's standard
Reversible reading	mm / inch
Interface	USB interface
Interface	Digimatic interface
IP Index of Protection	IP 67
Measured value saving	Once-off setting of the zero position
Measurement technology	digital
Calibration	C7
Type of product	Internal quick calipers

## Services

Calibration External / internal quick caliper	013850
Labelling laser-etched Type	018940
DAkkS calibration External / internal quick caliper	011320

## Accessories

Alkaline manganese battery set International size LR3	081555 LR3
Alkaline-manganese batteries International size LR3	081556 LR3

Transmitter Type S2	498966 S2
Connecting cable Type USB2	497440 USB2
Interface adapter Type A2	498954 A2
Connecting cable Type D2	497440 D2
Connecting cable Type D1	497440 D1
Multi-receiver / USB keyboard interface	498975
Receiver / USB keyboard interface	498965