

Kroepelin
Längenmesstechnik

External quick caliper with dial gauge for pipes, Measuring range: 0-20mm



Order data

Order number	438560 0-20
GTIN	2050001036773
Item class	46Q

Description

Version:

1 fixed and 1 movable arm with carbide spherical contact points. The deflection of the moving contact point is transmitted to the dial indicator. The measured result can be read directly.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Technical description

Scale divisions	0.01 mm
Measuring range	0 - 20 mm
maximum contact point length L (measurement depth)	80 mm
minimum bore \varnothing	10 mm
Dial indicator \varnothing	65 mm
Carbide spherical point \varnothing	1.5 mm
IP Index of Protection	IP 65
Error limit	0.03 mm
Standard	Manufacturer's standard
Measurement technology	analogue

Calibration	C7
Type of product	External quick callipers

Services

CalibrationExternal / internal quick caliper Type S	023450 S
DAkkS calibrationExternal / internal quick caliper Type S	023460 S