

Kroepelin
Längenmesstechnik**Internal quick caliper, Measuring range: 20-40mm****Order data**

Order number	438950 20-40
GTIN	2050001036865
Item class	46Q

Description**Version:**

1 fixed and 1 movable arm with carbide spherical contact points. The deflection of the moving contact point is transmitted to the dial indicator. The measured result can be read directly.

Function:

IP65: Protected against jets of water from all directions and protected against penetration by dust (dust-tight), also completely protected against touching.

Technical description

minimum groove width	1.5 mm
maximum contact point length L (measurement depth)	80 mm
Scale divisions	0.01 mm
Measuring range	20 - 40 mm
maximum groove depth	7 mm
Carbide spherical point \varnothing	1 mm
Error limit	0.03 mm
Dial indicator \varnothing	65 mm
Calibration	C7
IP Index of Protection	IP 65

Standard	Manufacturer's standard
Measurement technology	analogue
Type of product	Internal quick caliper

Services

DAkkS calibrationExternal / internal quick caliper Type S	023460 S
CalibrationExternal / internal quick caliper Type S	023450 S