

**Feeler gauge shim roll 25 mm×5 m, Carbon steel, Thickness: 0,4mm****Order data**

Order number	478520 0,4
GTIN	2050001054401
Item class	48B

**Description****Version:**

Cold rolled, hard spring feeler strip steel of maximum precision. From size 0.02, the strip thickness is continuously marked and cannot be wiped off (exception: for No. 478502 from size 0.08).

Stored in a practical dispenser; pull out like a tape measure. The desired length can be cut from the 5 or 10 m long strip.

**C-steel** – Carbon steel, material No. 1.1274, cold rolled, hardened, bright surface. **(size 0.01 and 0.02 stainless).**

**Application:**

In jig and tool building for aligning and adjusting machine parts, as a shim for aligning components, for tolerance measurements of all kinds, for checking fits and guides, for setting up printing rollers.

**Technical description**

Thickness	0.4 mm
Error limit	±9 µm
Standard	Works standard

Material	Carbon steel
Roll length	5 m
Roll width	25 mm
Type of product	Feeler gauge shim strip